



Easy-to-Manage, Super Simple 1 Chip DLP[™] Laser Projector delivers Clear Pictures in Bright Rooms with Flexible Integration in the Classroom or Office

PT-FRZ60

DLP[™] imaging technology, Quartet Colour Harmonizer, Rich Colour Enhancer, and digitally modulated Dynamic Contrast 2 optimization coalesce in images of surpassing brightness, colour, and clarity regardless of ambient light levels. Flexible 2.0x zoom lens with V/H Lens-Shift joins DIGITAL LINK and CEC-ready HDMI® terminals supporting 4K/60p input signals*2. Separate LAN terminal and USB-DC outlet further streamline installation. Operation is almost

Key Features

Laser 1-chip DLP, 6,000 lumens, WUXGA

DLP[™] imaging technology, Quartet Colour Harmonizer, Rich Colour Enhancer, and digitally modulated Dynamic Contrast 2 optimization

Maintenance free up to 20,000 hours with dust-resistant optical block and long lasting laser engine

Flexible 2.0x zoom lens (1.46 – 2.94:1) with V/H Lens-Shift

Support uncompressed 4K/60p input signals via HDCP 2.2compliant HDMI® inputs or DIGITAL LINK terminal







Panasonic CONNECT





Projector type



1-Chip DLP^{TM} projector



PT-FRZ60

https://ap.connect.panasonic.com/id /en/products/projectors/pt-frz60

Projector type	1-Chip DLP*** projector
Display method	DLP TM chip x 1, DLP TM projection system
Display Device -> Panel size	17.0 mm (0.67 in) diagonal (16:10 aspect ratio)
Display Device -> Number of pixels	2,304,000 (1920 x 1200 pixels)
Light source	Laser diodes
Light output *1	6,000 lm
Light output (ANSI)	6,000 lm
Light output (Center) ^{*1 *2}	6,200 lm (Center)
Time until light output declines to 50 %	%20,000 hours [NORMAL]
-> NORMAL ^{*4}	
Resolution	1920 x 1200 pixels
Contrast Ratio (typ.) ^{*2}	20,000:1 (Full On/Full Off, Picture Mode: Dynamic, Dynamic Contrast 1, Operating Mode:
	Normal)
Screen size (diagonal)	1.02–7.62 m (40–300 in), 16:10 aspect ratio
Center-to-corner zone ratio	90%
Lens	2.0x manual zoom (throw ratio: 1.46–2.94:1), manual focus, F 2.0–3.4, f 21.5–43.0 mm
Lens shift -> Vertical(from center of	+64 %, -44 % (manual)
	+04 %, -44 % (Inditudi)
screen)	
Lens shift -> Horizontal(from center	+34 %, -27 % (manual)
of screen)	
Keystone correction range	Vertical: ±40 °, Horizontal: ±20 °
Installation	Ceiling/floor, front/rear, free 360-degree installation
Terminals -> HDMI [™] IN	HDMI TM 19-pin x 2 (Compatible with HDCP 2.3, Deep Color, 4K/60p signal input*4), CEC
	supported
Terminals -> COMPUTER IN (D-SUB	D-sub HD 15-pin (female) x 1 (RGB/YPBPR/YCBCR)
15pin)	· · · · · · · · · · · · · · · · · · ·
	D-sub HD 15-pin (female) x 1 (RGB/YP _B P _R /YC _B C _R)
15pin)	υ σαστιστισ-pin (remaic) × τ (reduite Ber R/TeBeR)
•	Din jask v 1 (composite video)
Terminals -> VIDEO IN	Pin jack x 1 (composite video)
Terminals -> AUDIO IN(M3 Stereo	Pin jack x 1 (L, R)
Mini Jack)	
Terminals -> AUDIO IN(Pin Jack L/R)	M3 x 1/M3 x 1
Terminals -> AUDIO OUT(M3 Stereo	M3 x 1 (Variable)
Mini Jack)	
Terminals -> SERIAL IN	D-sub 9-pin (female) x 1 for external control (RS-232C compliant)
Terminals -> DIGITAL LINK IN / LAN	RJ-45 x 1 for network and DIGITAL LINK connections (HDBaseT TM compliant), PJLink TM
	(Class 2) compatible, 100Base-TX, Art-Net compatible, HDCP 2.3 compatible, Deep Color
	compatible, 4K/60p signal input*4
Terminals -> LAN	RJ-45 x 1 for network connection, PJLink TM (Class 2) compatible, 10Base-T/100Base-TX,
	Art-Net compatible
	· · · · · · · · · · · · · · · · · · ·
Terminals -> USB TYPE A	USB connector (Type A) x 1 (Output 5 V/2 A)
Power supply	AC 100–240 V, 50/60 Hz
Maximum power consumption *11	540 W (5.8-2.3 A)
On-mode power	[NORMAL] 490 W
consumption(Operating mode) ->	
Normal ^{*11}	
Normal ^{*11} On-mode power	[ECO] 385 W
On-mode power	
On-mode power consumption(Operating mode) -> Eco	
On-mode power consumption(Operating mode) -> Eco *11	
On-mode power consumption(Operating mode) -> Eco *11 On-mode power	
On-mode power consumption(Operating mode) -> Eco *11 On-mode power	
On-mode power consumption(Operating mode) -> Eco *11 On-mode power consumption(Operating mode) -> Quiet ^{*11}	[QUIET] 385 W
On-mode power consumption(Operating mode) -> Eco *11 On-mode power consumption(Operating mode) -> Quiet ^{*11} Standby power consumption ->	
On-mode power consumption(Operating mode) -> Eco *11 On-mode power consumption(Operating mode) -> Quiet ^{*11} Standby power consumption -> Normal	[QUIET] 385 W 10 W (Standby Mode) [NORMAL]
On-mode power consumption(Operating mode) -> Eco *11 On-mode power consumption(Operating mode) -> Quiet ^{*11} Standby power consumption -> Normal Standby power consumption -> ECO	[QUIET] 385 W 10 W (Standby Mode) [NORMAL] 0.5 W (Standby Mode) [ECO]
On-mode power consumption(Operating mode) -> Eco *11 On-mode power consumption(Operating mode) -> Quiet ^{*11} Standby power consumption -> Normal Standby power consumption -> ECO Cabinet materials	[QUIET] 385 W 10 W (Standby Mode) [NORMAL] 0.5 W (Standby Mode) [ECO] Molded plastic
On-mode power consumption(Operating mode) -> Eco *11 On-mode power consumption(Operating mode) -> Quiet ^{*11} Standby power consumption -> Normal Standby power consumption -> ECO Cabinet materials Filter	[QUIET] 385 W 10 W (Standby Mode) [NORMAL] 0.5 W (Standby Mode) [ECO]
On-mode power consumption(Operating mode) -> Eco *11 On-mode power consumption(Operating mode) -> Quiet ^{*11} Standby power consumption -> Normal Standby power consumption -> ECO Cabinet materials Filter	[QUIET] 385 W 10 W (Standby Mode) [NORMAL] 0.5 W (Standby Mode) [ECO] Molded plastic
On-mode power consumption(Operating mode) -> Eco *11 On-mode power consumption(Operating mode) -> Quiet *11 Standby power consumption -> Normal Standby power consumption -> ECO Cabinet materials Filter Operation noise -> Normal *2	[QUIET] 385 W 10 W (Standby Mode) [NORMAL] 0.5 W (Standby Mode) [ECO] Molded plastic No
On-mode power consumption(Operating mode) -> Eco *11 On-mode power consumption(Operating mode) -> Quiet *11 Standby power consumption -> Normal Standby power consumption -> ECO Cabinet materials Filter Operation noise -> Normal *2 Operation noise -> Quiet *2	[QUIET] 385 W 10 W (Standby Mode) [NORMAL] 0.5 W (Standby Mode) [ECO] Molded plastic No 35 dB [NORMAL]
On-mode power consumption(Operating mode) -> Eco *11 On-mode power consumption(Operating mode) -> Quiet *11 Standby power consumption -> Normal Standby power consumption -> ECO Cabinet materials Filter Operation noise -> Normal *2 Operation noise -> Quiet *2 Dimensions (W x H x D)	[QUIET] 385 W 10 W (Standby Mode) [NORMAL] 0.5 W (Standby Mode) [ECO] Molded plastic No 35 dB [NORMAL] 30 dB [QUIET] 498 x 168*5 x 492 mm (19 5/8″ x 6 5/8″*5 x 19 3/8″)
On-mode power consumption(Operating mode) -> Eco *11 On-mode power consumption(Operating mode) -> Quiet *11 Standby power consumption -> Normal Standby power consumption -> ECO Cabinet materials Filter Operation noise -> Normal *2 Operation noise -> Quiet *2 Dimensions (W x H x D) Dimensions -> Width (including	[QUIET] 385 W 10 W (Standby Mode) [NORMAL] 0.5 W (Standby Mode) [ECO] Molded plastic No 35 dB [NORMAL] 30 dB [QUIET]
On-mode power consumption(Operating mode) -> Eco *11 On-mode power consumption(Operating mode) -> Quiet *11 Standby power consumption -> Normal Standby power consumption -> ECO Cabinet materials Filter Operation noise -> Normal *2 Operation noise -> Normal *2 Dimensions (W x H x D) Dimensions -> Width (including protruding parts)	[QUIET] 385 W 10 W (Standby Mode) [NORMAL] 0.5 W (Standby Mode) [ECO] Molded plastic No 35 dB [NORMAL] 30 dB [QUIET] 498 x 168*5 x 492 mm (19 5/8″ x 6 5/8″*5 x 19 3/8″) 498 mm (19 5/8″)
On-mode power consumption(Operating mode) -> Eco *11 On-mode power consumption(Operating mode) -> Quiet *11 Standby power consumption -> Normal Standby power consumption -> ECO Cabinet materials Filter Operation noise -> Normal *2 Operation noise -> Normal *2 Dimensions (W x H x D) Dimensions -> Width (including protruding parts) Dimensions -> Height (including	[QUIET] 385 W 10 W (Standby Mode) [NORMAL] 0.5 W (Standby Mode) [ECO] Molded plastic No 35 dB [NORMAL] 30 dB [QUIET] 498 x 168*5 x 492 mm (19 5/8″ x 6 5/8″*5 x 19 3/8″)
On-mode power consumption(Operating mode) -> Eco *11 On-mode power consumption(Operating mode) -> Quiet *11 Standby power consumption -> Normal Standby power consumption -> ECO Cabinet materials Filter Operation noise -> Normal *2 Operation noise -> Normal *2 Operation noise -> Quiet *2 Dimensions (W x H x D) Dimensions -> Width (including protruding parts) Dimensions -> Height (including protruding parts)	[QUIET] 385 W 10 W (Standby Mode) [NORMAL] 0.5 W (Standby Mode) [ECO] Molded plastic No 35 dB [NORMAL] 30 dB [QUIET] 498 x 168*5 x 492 mm (19 5/8″ x 6 5/8″*5 x 19 3/8″) 498 mm (19 5/8″) 168 mm (6 5/8″)
On-mode power consumption(Operating mode) -> Eco *11 On-mode power consumption(Operating mode) -> Quiet *11 Standby power consumption -> Normal Standby power consumption -> ECO Cabinet materials Filter Operation noise -> Normal *2 Operation noise -> Normal *2 Operation noise -> Quiet *2 Dimensions (W x H x D) Dimensions -> Weidth (including protruding parts) Dimensions -> Height (including protruding parts) Dimensions -> Depth (including lens)	[QUIET] 385 W 10 W (Standby Mode) [NORMAL] 0.5 W (Standby Mode) [ECO] Molded plastic No 35 dB [NORMAL] 30 dB [QUIET] 498 x 168*5 x 492 mm (19 5/8" x 6 5/8"*5 x 19 3/8") 498 mm (19 5/8") 168 mm (6 5/8") 492 mm (19 3/8")
On-mode power consumption(Operating mode) -> Eco *11 On-mode power consumption(Operating mode) -> Quiet *11 Standby power consumption -> Normal Standby power consumption -> ECO Cabinet materials Filter Operation noise -> Normal *2 Operation noise -> Normal *2 Operation noise -> Quiet *2 Dimensions (W x H x D) Dimensions -> Width (including protruding parts) Dimensions -> Height (including protruding parts)	[QUIET] 385 W 10 W (Standby Mode) [NORMAL] 0.5 W (Standby Mode) [ECO] Molded plastic No 35 dB [NORMAL] 30 dB [QUIET] 498 x 168*5 x 492 mm (19 5/8″ x 6 5/8″*5 x 19 3/8″) 498 mm (19 5/8″) 168 mm (6 5/8″)
On-mode power consumption(Operating mode) -> Eco *11 On-mode power consumption(Operating mode) -> Quiet *11 Standby power consumption -> Normal Standby power consumption -> ECO Cabinet materials Filter Operation noise -> Normal *2 Operation noise -> Normal *2 Operation noise -> Quiet *2 Dimensions (W x H x D) Dimensions -> Weidth (including protruding parts) Dimensions -> Height (including protruding parts) Dimensions -> Depth (including lens)	[QUIET] 385 W 10 W (Standby Mode) [NORMAL] 0.5 W (Standby Mode) [ECO] Molded plastic No 35 dB [NORMAL] 30 dB [QUIET] 498 x 168*5 x 492 mm (19 5/8" x 6 5/8"*5 x 19 3/8") 498 mm (19 5/8") 168 mm (6 5/8") 492 mm (19 3/8") Approx. 16.1 kg (35.5 lbs)
On-mode power consumption(Operating mode) -> Eco *11 On-mode power consumption(Operating mode) -> Quiet *11 Standby power consumption -> Normal Standby power consumption -> ECO Cabinet materials Filter Operation noise -> Normal *2 Operation noise -> Quiet *2 Dimensions (W x H x D) Dimensions -> Width (including protruding parts) Dimensions -> Height (including protruding parts) Dimensions -> Depth (including lens) Weight *13	[QUIET] 385 W 10 W (Standby Mode) [NORMAL] 0.5 W (Standby Mode) [ECO] Molded plastic No 35 dB [NORMAL] 30 dB [QUIET] 498 x 168*5 x 492 mm (19 5/8" x 6 5/8"*5 x 19 3/8") 498 mm (19 5/8") 168 mm (6 5/8") 492 mm (19 3/8") Approx. 16.1 kg (35.5 lbs)

Operating Environment -> Operating humidity (No condensation)	10–80 % (no condensation)
Applicable software	Logo Transfer Software, Multi Monitoring & Control Software, Early Warning Software
Footnote Description	 When [PICTURE MODE] is set to [DYNAMIC], [DAYLIGHT VIEW] is set to [OFF], [DYNAMIC CONTRAST] is set to [OFF], [LIGHT OUTPUT] is set to [100%], and [AUTO POWER SAVE] is set to [OFF].
	 Measurement, measuring conditions, and method of notation all comply with ISO/IEC 21118: 2020 international standards. Value is the average of all products when shipped.
	 Measurement, measuring conditions, and method of notation all comply with American National Standards Institute standards. Value is the average of all products when shipped.
	Average light-output value of all shipped products measured at the center of th screen.
	5. Around this time, light output will have decreased by approximately 50 %. IEC62087: 2008 Broadcast Contents, Normal Mode, Dynamic Contrast 2, temperature 30 °C (86 °F), elevation 700 m (2,297 ft) with 0.15 mg/m3 of airborn particulate matter. Estimated time until light output declines to 50 % varies depending on environment.
	6. 4K signals are converted to the projector's resolution (1920 x 1200 pixels) upon projection. Supported terminals: DIGITAL LINK/HDMI®.
	7. With legs at shortest position.
	8. Average value. May differ depending on the actual unit.